



DENTAL MILLING



WE'VE GOT
YOUR BACK



DEPRAG

D52 - ADC

5-Axis dry milling machine with automatic disc changer



Loniser module.



10 tools.
Tool lifetime monitoring system.



Servo motor
Highly precise position control.



One-piece cast aluminum structure.



Automatic teeth removal.



RFID disc intelligent identification.



Remote monitoring system.



Ball screw rod
Smooth movement, precise positioning.

Powerful Spindle

1.8 kW
62 mm
60000 RPM




Spindle

Water cooling
cooling method



Industrial Chiller

Automatic Disc Changer



-8slot

Adopting servo-electric jaws and flexible mechanical structure of discs changing module.

Automatic calibration.

After the calibration module is installed, the device can be automatically calibrated.



Applications



Crown/Bridge



Inlays/Onlays



Abutments



Veneer



Denture



Occlusal splint



Screw-retained bridge



Surgical guide



Model cast

Holder Types



Half-open blank holder (C-CLAMP)

- Standard
- Enables -5axis milling up to 90 degrees axis adjustment (+30° , -90°)
- Maximum material thickness 35mm



Block holder

- Standard
- 6 positions, suitable for zirconia and PMMA block
- 18*13*15/20*15*14/20*15*19/40*15*14/40*15*19/55*15.5*19 available



Round closed clamp holder

- Standard
- Maximum material thickness 35mm

Materials



Zirconia



PMMA



PEEK



Wax